

# BEG 1000 B



This dispersion system can generate high mass flows continuously, e.g., 6 kg/h, with optimal dosing constancy.

## BENEFITS

- Excellent short-term and long-term dosing constancy
- Easy to operate
- Quick and easy to clean
- Remote control or computer-controlled
- Pulse mode
- Easy to fill while in operation
- Large reservoir (1,500 cm<sup>3</sup>)
- Robust design, proven in industrial applications
  
- Reliable function
- Reduces your operating expenses
- Low maintenance

## APPLICATIONS

- Filter industry: Loading test of
  - Engine filters as per ISO 5011
  - Hot gas filters
  - Bag filters
  - Air filters
  - Cyclones
- Chemical and pharmaceutical industry
- Cement industry

## DATASHEET

Particle size range	0.1 – 200 $\mu\text{m}$
Maximum particle number concentration	Ca. $10^7$ particles/ $\text{cm}^3$
Volume flow	80–165 $\text{NI}/\text{min}$
Mass flow (particles)	Type B: 100 – 6,000 $\text{g}/\text{h}$ (with reference to SAE Fine, A2 dust)
Filling quantity	500 g
Power supply	115 – 230 V, 50/60 Hz
Particle material	Non-cohesive powders and bulks
Dosing time	Several hours nonstop
Pre-pressure	4 – 8 bar
Carrier/dispersion gas	Random (generally air)
Compressed air connection	Quick coupling
Aerosol outlet connection	Type B: $\varnothing_{\text{inside}} = 8 \text{ mm}$ , $\varnothing_{\text{outside}} = 12 \text{ mm}$
Reservoir volume	1,500 $\text{cm}^3$
Dimensions	Dosing unit: 610 • 260 • 340 mm (H • W • D), control unit: 195 • 260 • 340 mm (H • W • D)