# Р**R**ОМО<sup>®</sup> 1000 Н





The aerosol sensor welas \$\mathbb{8}\$ 1100 HP and aerosol sensor welas \$\mathbb{8}\$ 1200 HP are equipped with a heatable and, as required, pressure-tight cuvette to ensure isobaric and isothermal sampling into the sensor's measurement volume. The Promo \$\mathbb{8}\$ 1000 H model variant also offers heating regulation for temperatures up to 120 °C for the welas \$\mathbb{8}\$ 1100 HP and welas \$\mathbb{8}\$ 1200 HP aerosol sensors with heatable cuvette. The Promo \$\mathbb{8}\$ is usually calibrated for the operating volume flow. In the Promo \$\mathbb{8}\$ 1000 H version, regulation of the sampling volume flow is performed independently by the customer taking the temperature and pressure into consideration.

### **OPERATION PRINCIPLE**



#### **BENEFITS**

- Very high size resolution
- Concentration range from < 1 particle/cm<sup>3</sup> to 5 10<sup>5</sup> particles/cm<sup>3</sup>
- Calibration curves for different refractive indices
- Very high and reproducible counting efficiency even from 0.12  $\mu m$
- High temporal resolution of up to 10 ms
- Calibration, cleaning, and lamp replacement can be performed independently by the customer
- External control via RS 232 or Ethernet
- Low maintenance, reduces operating costs



## **DATASHEET**

Measuring principle	Optical light-scattering
Measurement range (number C <sub>N</sub> )	< 5 • 10 <sup>5</sup> particles/cm <sup>3</sup>
Measurement range (size)	0.2 – 10 μm, 0.3 – 17 μm, 0.6 – 40 μm
Volume flow	5 l/min, 1.6 l/min
Size channels	Max. 128 (64/decade)
Time resolution	1 s
Interfaces	USB, Ethernet (LAN), Wi-Fi, RS-232/485
User interface	Touchscreen, 800 • 480 pixel, 7" (17.78 cm)
Data logger storage	4 GB Compact Flash
Software	PDControl, FTControl, PDAnalyze
Thermodynamic conditions	+10 - +40 °C, -100 - 50 mbar
Data acquisition	Digital, 20 MHz processor, 256 raw data channels
Light source	Xenon high pressure lamp 75 W
Gehäuse	Table housing, optional: with mounting brackets for rack-mounting
Support options	Direct remote access, Palas webserver service
Operating system	Windows embedded
Power supply	115 – 230 V, 50/60 Hz
Power consumption	100 W
Installation conditions	+5 – +40 °C (control unit)
Dimensions	185 • 450 • 315 mm (H • W • D) (19")
Weight	Control unit: approx. 8 kg, sensor: approx. 18 kg



#### **APPLICATIONS**

- Separation efficiency determination of automotive cabin air filters, engine air filters, ambient air filters, compressed air filters, vacuum cleaner filters, cleanable filters, electrostatic precipitators, oil separators, cooling lubricant separators, wet separators, cyclones, and other separators
- Isothermal and isobaric particle size and quantity determination, e.g., in the automotive, chemical, pharmaceutical, and food industries
- Investigation of fast, transient processes
- Particle measurement for cloud formation
- Emission measurements



Mehr Informationen:

https://www.palas.de/en/product/promo1000h