

# BEG 1000 A



This dispersion system can continuously generate low mass flows, e.g., 8 g/h, with optimal dosing constancy.

## BENEFITS

- Excellent short-term and long-term dosing constancy
- Easy to operate
- Quick and easy to clean
- Remote control or computer-controlled
- Pulse mode
- Easy to fill while in operation
- Large reservoir (1,500 cm<sup>3</sup>)
- Robust design, proven in industrial applications
  
- Reliable function
- Reduces your operating expenses
- Low maintenance

## APPLICATIONS

- Filter industry: Loading test of
  - Engine filters as per ISO 5011
  - Hot gas filters
  - Bag filters
  - Air filters
  - Cyclones
- Chemical and pharmaceutical industry
- Cement industry

## DATASHEET

粒径范围	0.1 – 200 $\mu\text{m}$	颗粒物最大数量浓度	Ca. $10^7$ particles/ $\text{cm}^3$
体积流量	80–165 $\text{NI}/\text{min}$	Mass flow (particles)	Type A: 8 – 550 g/h (with reference to SAE Fine, A2 dust)
Filling quantity	500 g	Power supply	115 – 230 V, 50/60 Hz
Particle material	Non-cohesive powders and bulks	Dosing time	Several hours nonstop
Pre-pressure	4 – 8 bar	Carrier/dispersion gas	Random (generally air)
Compressed air connection	Quick coupling	Aerosol outlet connection	Type A: $\varnothing_{\text{inside}} = 6.4$ mm, $\varnothing_{\text{outside}} = 10$ mm
Reservoir volume	1,500 $\text{cm}^3$	Dimensions	Dosing unit: 610 • 260 • 340 mm (H • W • D), control unit: 195 • 260 • 340 mm (H • W • D)