

BEG 1000 C



This dispersion system can continuously generate the highest mass flows, e.g., 7.3 kg/h, with the highest dosing constancy.

BENEFITS

- Excellent short-term and long-term dosing constancy
- Easy to operate
- Quick and easy to clean
- Remote control or computer-controlled
- Pulse mode
- Easy to fill while in operation
- Large reservoir (1,500 cm³)
- Robust design, proven in industrial applications
- Reliable function
- Reduces your operating expenses
- Low maintenance

APPLICATIONS

- Filter industry: Loading test of
 - Engine filters as per ISO 5011
 - Hot gas filters
 - Bag filters
 - Air filters
 - Cyclones
- Chemical and pharmaceutical industry
- Cement industry

DATASHEET

粒径范围	0.1 – 200 μm	颗粒物最大数量浓度	Ca. 10^7 particles/ cm^3
体积流量	80–165 NL/min	Mass flow (particles)	Type C: 350 – 7,300 g/h (with reference to SAE Fine, A2 dust)
Filling quantity	500 g	Power supply	115 – 230 V, 50/60 Hz
Particle material	Non-cohesive powders and bulks	Dosing time	Several hours nonstop
Pre-pressure	4 – 8 bar	Carrier/dispersion gas	Random (generally air)
Compressed air connection	Quick coupling	Aerosol outlet connection	Type C: $\varnothing_{\text{inside}} = 8 \text{ mm}$, $\varnothing_{\text{outside}} = 12 \text{ mm}$
Reservoir volume	1,500 cm^3	Dimensions	Dosing unit: 610 • 260 • 340 mm (H • W • D), control unit: 195 • 260 • 340 mm (H • W • D)