# **DEMC 2000**







The DEMC size classifier (as defined in ISO 15900) selects aerosol particles based on their electrical mobility and directs them to the outlet. It is also often referred to as a DMA.

The size classifier is suitable in combination with condensation particle counters from the Palas UF-CPC, ENVI-CPC series or electrometers (Charme®) for measuring the number concentrations of different aerosols in scientific and regulatory environments. Alternatively, columns and particle counters from other manufacturers can also be integrated.

### 优势

- The user is able to select any size within the defined size range.
- The DEMC can be connected to many counters to form an SMPS.
- Continuous and fast-scanning principle of measurement
- Graphic display of measurement values
- Intuitive operation using 7" touchscreen and GUI
- Integrated data logger
- · Low maintenance
- Reliable function
- Reduces your operating expenses

### 应用领域

- Calibration of condensation particle counters (CPC)
- Monodisperse particle source
- System component of an SMPS

#### **MODEL VARIATIONS**



#### **DEMC 2000 X**

Differential electrical mobility classifier from 8-1,400 nm with integrated X-ray ionization https://www.palas.de/zh/product/demc2000x



## 技术数据

Volume flow (sheath air)	2.5 – 14 l/min (others on request)	Size channels	Max. 256 (128/decade)
User interface	Touchscreen, 800 • 480 pixel, 7" (17.78 cm)	Data logger storage	4 GB
软件	PDAnalyze	Classifying range (size)	4 – 1,489 nm
Installation conditions	+5 – +40 °C (control unit)	Impaktor	Nozzle for 3 different cut-offs
Adjustment range (voltage)	1 – 10,000 V	Data Management	Prepared for connection to the Palas Cloud MyAtmosphere ("MyAtmosphere-ready"); Internet access and separate registration required. The MyAtmosphere terms of use apply.

## 标准和证书

ISO 15900:2010, CEN/TS 17434:2020