# **RBG 1000 ISD**





This device disperses particles at positive pressure values of up to 3 bar and can also use nitrogen and air as the dispersing gas. Optional operation with low pressure from 300 mbar absolute is possible. The 7-, 10-, 14- or 20-mm feed stock reservoirs are pressure-resistant. For operation with low pressure special pressure-resistant feed stock reservoirs are needed. Their piston is strongly connected to the feeding unit by a claw. This enables an undisturbed operation with low pressure.

The solid material reservoir with a diameter of 28 mm is not pressure-resistant, but can be used with the RBG 1000 SD under atmospheric conditions.

### 工作原理

**RBG 1000 ISD** 



### 优势

- Pressure-resistant up to 3 barg overpressure
- 2 m distance between dispersing unit and control unit
- Optional:Low pressure operation from 300 mbar absolute
- Nitrogen as dispersing gas
- Optional: Remote control or computer-controlled



## 技术数据

粒径范围	0.1 – 100 μm
颗粒物最大数量浓度	Ca. 10 <sup>7</sup> particles/cm <sup>3</sup>
体积流量	$0.5 - 5.0 \text{ m}^3/\text{h}$
Mass flow (particles)	0.04 – 430 g/h (with an assumed compacted density of 1 g/cm <sup>3</sup> )
Filling height	70 mm
Filling quantity	2.7 g (reservoir $\emptyset$ = 7 mm), 5.5 g (reservoir $\emptyset$ = 10 mm), 10.8 g (reservoir $\emptyset$ = 14 mm), 22 g (reservoir $\emptyset$ = 20 mm), 43 g (reservoir $\emptyset$ = 28 mm)
电源	115 – 230 V, 50/60 Hz
Particle material	Non-cohesive powders and bulks
Dosing time	Several hours nonstop
Pre-pressure	4 – 8 bar
Carrier/dispersion gas	Air, nitrogen
Maximum counter pressure	0.2 barg
Compressed air connection	Quick coupling
Feed rate	5 – 700 mm/h
Reservoir inner diameter	7, 10, 14, 20 mm
Aerosol outlet connection	Dispersion cover type A: $\emptyset_{inside} = 5$ mm, $\emptyset_{outside} = 8$ mmDispersion cover type B: $\emptyset_{inside} = 3.6$ mm, $\emptyset_{outside} = 6$ mmDispersion cover type: $\emptyset_{inside} = 2.5$ mm, $\emptyset_{outside} = 6$ mm
Dispergierdeckel	Type A, type B, type C, type D
Dimensions	Dispersion unit: 430 • 300 • 180 mm (H • W • D)
重量	Approx. 19 kg



### 应用领域

- All applications pressure-resistant up to 3 barg overpressure
- Dispersion of radioactive substances
- Dispersion of pharmaceutical powders
- Filter industry:
  - Determination of fractional separation efficiency
  - Determination of total separation efficiency
  - Long-term dusting
  - Filter media and ready-made filters
  - Dust removal filters
  - Vacuum cleaners and vacuum cleaner filters
  - Car interior filters
  - Engine air filters
- Calibration of particle measurement devices
- Flow visualization
- Inhalation tests
- Tracer particles for LDA, PIV, etc.
- Coating of surfaces



Mehr Informationen:

https://www.palas.de/zh/product/rbg1000isd