

WELAS[®] DIGITAL 2000 H



The aerosol sensors welas[®] 2070 H, HP, 2100 H, HP, 2200 H, HP, 2300 H, HP, and welas[®] 2500 H, HP are equipped with a heatable and, as required, pressure-tight cuvette to ensure isobaric and isothermal sampling into the sensor's measurement volume.

The welas[®] digital 2000 H model variant also offers heating regulation for temperatures up to 250 °C for the aerosol sensors with a heatable cuvette. The welas[®] digital is usually calibrated for the operating volume flow. In the welas[®] digital 2000 H version, the customer's regulation of the sampling volume flow is performed independently, taking the temperature and pressure into consideration.

优势

- Measuring range of 0.2 to 100 μm (4 measuring ranges selectable in one device)
- Up to four measuring ranges in only one device:
 - 0,2 μm – 10 μm
 - 0,3 μm – 17 μm
 - 0,6 μm – 40 μm
 - 2 μm – 100 μm (additionally for sensors 2300 and 2500)
- Up to 128 size channels per measuring range
- Concentration range of 1 particle/ cm^3 to 10^6 particles/ cm^3
- Calibration curves for different refractive indices
- Very high and reproducible counting efficiency rate starting at 0.2 μm (see Graph 2)
- High temporal resolution down to 10 ms
- Optical fiber technology
- Measurement in a potentially explosive environment
- Long service life of the light source of 2000 h
- Extensive PDControl and FTControl software
- Simple operation
- Calibration, cleaning, and lamp replacement can all be performed independently by the customer
- Low maintenance

应用领域

- Separation efficiency determination of automotive cabin air filters, engine air filters, ambient air filters, compressed air filters, vacuum cleaner filters, cleanable filters, electrostatic precipitators, oil separators, cooling lubricant separators, wet separators, cyclones, and other separators
- Isothermal and isobaric particle size and quantity determination, e.g., in the automotive, chemical, pharmaceutical, and food industries
- Investigation of fast, transient processes
- Test of smoke detectors
- Particle measurement for cloud formation
- Emission measurements
- Breathing function: inhalate / exhalate (particle size and number)

技术数据

测量原理	Optical light-scattering	测量范围(数量浓度)	$< 1 \cdot 10^6 \text{ particles/cm}^3$
测量范围(粒径)	0.2 – 10 μm , 0.3 – 17 μm , 0.6 – 40 μm , 2 – 100 μm	体积流量	5 l/min
Size channels	Max. 64/decade	接口	USB
User interface	Laptop	软件	PDControl, FTControl
Thermodynamic conditions	$\leq 250^\circ\text{C}$, -100 – 50 mbar	Data acquisition	Digital, 20 MHz processor, 256 raw data channels
Light source	Xenon arc lamp 35 W	外壳	Table housing, optional: with mounting brackets for rack-mounting
电源	115 – 230 V, 50/60 Hz	Installation conditions	+5 – +40 $^\circ\text{C}$ (control unit)
Dimensions	185 • 450 • 315 mm (H • W • D) (19")	重量	Control unit: approx. 18 kg, sensor: approx. 2.8 kg