

WELAS[®] DIGITAL 3000 HP



The aerosol sensors welas[®] 2070 HP, 2100 HP, 2200 HP, 2300 HP, and welas[®] 2500 HP are equipped with a cuvette heatable up to 120 °C and pressure-tight up to 10 barg to ensure isobaric and isothermal sampling into the sensor's measurement volume. The welas[®] digital system is usually calibrated for the operating volume flow. As the operating volume flow changes with pressure and temperature, it is advantageous for the user if automatic volume flow regulation for the sampling volume flow is provided for in the device.

In the welas[®] digital 3000 HP, the pressure and temperature of the carrier gas are measured, and the required operating volume flow is automatically set to 5 l/min.

工作原理

Includes:

- Mass flow controller for volume flow regulation
- Heating regulator up to 120 °C
- Temperature sensor
- Absolute pressure capsule
- Filter unit to protect the flow rate control

优势

- Measuring range of 0.2 to 100 μm (4 measuring ranges selectable in one device)
- Up to four measuring ranges in only one device:
 - 0,2 μm – 10 μm
 - 0,3 μm – 17 μm
 - 0,6 μm – 40 μm
 - 2 μm – 100 μm (additionally for sensors 2300 and 2500)
- Up to 128 size channels per measuring range
- Concentration range of 1 particle/ cm^3 up to 10^6 particles/ cm^3
- Calibration curves for different refractive indices
- Very high and reproducible counting efficiency rate starting at 0.2 μm (see Graph 2)
- High temporal resolution down to 10 ms
- Optical fiber technology
- Measurement in potentially explosive environment
- Long service life of the light source of 2000 h
- Extensive PDControl

- Simple operation
- Calibration, cleaning and lamp replacement can all be performed independently by the customer
- Low maintenance
- Reliable function
- Reduces your operating expenses

技术数据

| | |
|--------------------------|--|
| 测量原理 | Optical light-scattering |
| 测量范围(数量浓度) | $< 1 \cdot 10^6 \text{ particles/cm}^3$ |
| 测量范围(粒径) | 0.2 – 10 μm , 0.3 – 17 μm , 0.6 – 40 μm , 2 – 100 μm |
| 体积流量 | 5 l/min |
| Size channels | Max. 64/decade |
| Time resolution | $\geq 10 \text{ ms}$ |
| 接口 | USB |
| User interface | Laptop |
| 软件 | PDControl |
| Thermodynamic conditions | $\leq 120^\circ\text{C}$, $\leq 10 \text{ bar}$ |
| Data acquisition | Digital, 20 MHz processor, 256 raw data channels |
| Light source | Xenon arc lamp 35 W |
| 外壳 | Table housing, optional: with mounting brackets for rack-mounting |
| 电源 | 115 – 230 V, 50/60 Hz |
| Installation conditions | +5 – +40 °C (control unit) |
| Dimensions | 185 • 450 • 315 mm (H • W • D) (19") |
| 重量 | Control unit: approx. 18 kg, sensor: approx. 2.8 kg |

应用领域

- Separation efficiency determination of automotive cabin air filters, engine air filters, ambient air filters, compressed air filters, vacuum cleaner filters, cleanable filters, electrostatic precipitators, oil separators, cooling lubricant separators, wet separators, cyclones, and other separators
- Isothermal and isobaric particle size and quantity determination, e.g., in the automotive, chemical, pharmaceutical, and food industries
- Investigation of fast, transient processes
- Test of smoke detectors
- Particle measurement for cloud formation
- Emission measurements
- Breathing function: inhalate / exhalate (particle size and number)



Mehr Informationen:

<https://www.palas.de/zh/product/welasdigital3000HP>